



Panduct® G2X2WH6-A Base Wiring Duct

G2X2WH6-A

The G2X2WH6-A Panduct Lead-Free PVC Wide Slot Adhesive Wiring Duct feature a wide slot/finger design that provides greater sidewall rigidity and is suitable with a range of wire bundle sizes. UL 94 flame class of V-0 with a UL recognized continuous-use temperature up to 122°F (50°C). Adhesive and mounting holes provided. 2.0" x 2.0" (50.8 mm x 50.8 mm) and 6' (1.8 m) long. Cover sold separately. Color Light Gray.

Specifications

Note	Adhesive tape is not meant for permanent mounting of wiring duct. One mounting hole on each end will be exposed for permanent mounting with fasteners. For best results, wiring duct should be applied to clean, dry, grease-free surfaces. We recommend the surface be cleaned prior to wiring duct installation
Duct Dimensions (In.)	2.25W x 2.12H
Product Type	Base Wiring Duct
Application	Wide slot/finger design provides greater sidewall rigidity and can be used in a wide range of applications
Color	White
Cover Part Number	C2WH6
Flammability Rating	UL94 V-0
Includes	Base Only
Standards Met	RoHS Compliant, UL Recognized, CE Compliant
Material	PVC
Material Properties	Lead-Free
Mount Method	Mounting Holes with Adhesive
Measurement System	Imperial
Wiring Duct Style	Wide Slot Wiring Duct
Wiring Duct Type	G
Overall Length (ft.)	6
Overall Length (m)	1.8
Overall Width (In.)	2.25
Overall Width (mm)	57.2
Overall Height (In.)	2.12
Overall Height (mm)	53.8
Slot Width (In.)	0.31
Slot Width (mm)	7.9
Sub Brand	Panduct®

Specifications (continued)

Part Features	Wide finger and slot design provides greater rigidity and allows use with a wide range of wire and bundle sizes. Upper and lower scorelines allows easy finger and sidewall section removals.
---------------	---

Packaging Detail

UPC	07498354717
Std. Pkg. Qty.	6
Std. Pkg. Volume (cf)	0.1361
Std. Ctn. Qty.	120
Std. Ctn. Volume (cf)	2.7213