

Modular Cable Plug to Plug 8p8c (RJ45,
Ethernet) 25.00' (7.62m) Double Shielded

RoHS
Compliant

Stock No.: CAT8-25BK

FEATURES

- Strain Relief
- S/FTP
- 24 AWG
- Stranded Copper



Product Description

Cat.8 Ethernet Network Cables are capable to reach up to 40Gbps transfer speeds and up to 2GHz bandwidth using copper conductors and RJ45 connectors. Cat.8 patch cables are backwards compatible with all categories Cat.5E, Cat.6, Cat6A, Cat.7.

General Specifications

Attribute	Value
Terminated/Unterminated	Terminated
Connector Type	RJ45
Cable Type	Ethernet
Length	25.00' (7.62m)
Gauge	24 AWG
Conductor	Bare Copper
Shield/Unshielded	Shielded
Voltage Rating	30V
1.0 - 2000MHz Impedance (Ω)	100 $\pm$ 15
Maximum Operating Frequency	2000MHz
Operating & Storage Temp.	-40°C to 60°C -40°F to 140°F
Installation Temp.	-20°C to 60°C -4°F to 140°F
Jacket Color	Black

