

MQDC1-530

► SINGLE ENDED CORDSETS



Cordset: Single Ended M12
5-pin Straight Female
9 m (29.53 ft) 5x22 Black PVC Jacket
Nickel-Plated Brass Coupling Nut
Part Number: 47814

CERTIFICATIONS



SPECIFICATIONS

Cordset Length Range (m)	5.00-9.99
IP Rating	IP67
Connector 1 Type	M12
Connector 2 Type	Flying Leads
Number of Ends	Single Ended
Connector 1 Number of Contacts	5
Coupling Nut Material	Nickel Plated Brass
Cable Jacket Material	PVC
Cable Jacket Color	Black
Connector 1 Key Code	A
Connector 1 Gender	Female
Outside Cable Diameter (mm)	5.59
Cordset Length (m)	9.00
Connector 1 Orientation	Straight
Overmold Material and Color	PUR Black
Shield/No Shield	No Shield
Trunk Length (m)	No Trunk
Minimum Temp. (Celsius)	-40
Maximum Temp. (Celsius)	70
Current Rating (A)	4
Voltage Rating (V)	250 V ac/dc