

MQDEC-1703SS-DB25

► DOUBLE-ENDED CORDSETS



Cordset: Double Ended M12 to D-SUB
17-pin Straight Female; 25-pin Straight Male
1 m 17x26 Shielded Black PVC Jacket
Nickel-Plated Brass Coupling Nuts
Part Number: 806015

SPECIFICATIONS

Cordset Length Range (m)	Less than 2.00
Connector 1 Type	M12
Connector 2 Type	D-SUB
Number of Ends	Double Ended
Connector 1 Number of Contacts	17
Coupling Nut Material	Nickel Plated Brass
Connector 2 Number of Contacts	25
Cable Jacket Material	PVC
Cable Jacket Color	Black
Connector 1 Key Code	A
Connector 1 Gender	Female
Outside Cable Diameter (mm)	7.00
Connector 2 Gender	Male
Cordset Length (m)	1.00
Connector 1 Orientation	Straight
Connector 2 Orientation	Straight
Overmold Material and Color	PUR Black
Shield/No Shield	Shield - Tied to Coupling Nut
Trunk Length (m)	No Trunk
Minimum Temp. (Celsius)	-40
Maximum Temp. (Celsius)	105
Current Rating (A)	1.5
Voltage Rating (V)	50 V ac/dc