

# MQDEC-1703SS-USB

▶ DOUBLE-ENDED CORDSETS



Cordset: Double Ended M12 to USB-A  
17-pin Straight Female; 4-pin Straight Male  
1 m 17x26 Shielded Black PVC Jacket  
Nickel-Plated Brass Coupling Nuts  
Part Number: 806010

### SPECIFICATIONS

Cordset Length Range (m)	Less than 2.00
IP Rating	IP68
Connector 1 Type	M12
Connector 2 Type	USB-A
Number of Ends	Double Ended
Connector 1 Number of Contacts	17
Coupling Nut Material	Nickel Plated Brass
Connector 2 Number of Contacts	4
Cable Jacket Material	PVC
Cable Jacket Color	Black
Connector 1 Key Code	A
Connector 1 Gender	Female
Outside Cable Diameter (mm)	7
Connector 2 Gender	Male
Cordset Length (m)	1.00
Connector 1 Orientation	Straight
Connector 2 Orientation	Straight
Overmold Material and Color	PUR Black
Shield/No Shield	Shield - Tied to Coupling Nut
Trunk Length (m)	No Trunk
Minimum Temp. (Celsius)	-40
Maximum Temp. (Celsius)	70
Current Rating (A)	2.0
Voltage Rating (V)	125 V ac/dc