

Precision ESD Safe Dissipative Screwdrivers



272 Slotted Screwdriver, With Precision PicoFinish® ESD Safe Dissipative Handle Blade high alloy CVM steel. Handle manufactured from impact resistant, dissipative material. ESD standard IEC 61340-5-1.

Item	No.	mm	Inch	mm	Inch	mm	Inch
27270	.8	1/32	40	1.6	0.16	120	4.7
27271	1.0	.039	40	1.6	0.18	120	4.7
27272	1.2	3/64	40	1.6	0.20	120	4.7
27273	1.5	1/16	40	1.6	0.25	120	4.7
27274	2.0	5/64	40	1.6	0.40	120	4.7
27275	2.0	5/64	100	3.9	0.40	180	7.1
27276	2.5	3/32	50	2.0	0.40	145	5.7
27277	2.5	3/32	100	3.9	0.40	195	7.7
27278	3.0	1/8	50	2.0	0.50	145	5.7
27279	3.0	1/8	100	3.9	0.50	210	8.3
27280	3.5	9/64	60	2.4	0.60	170	6.7
27281	4.0	5/32	60	2.4	0.80	170	6.7

*Metric dimensions actual • Inch dimensions approximate



273 Phillips Screwdriver, With Precision PicoFinish® ESD Safe Dissipative Handle Blade high alloy CVM steel. Handle manufactured from impact resistant, dissipative material. ESD standard IEC 61340-5-1.

Item No.			Size	mm	inch			mm	inch
27330			000	40	1.6	2.0	.08	120	4.7
27331			00	40	1.6	2.0	.08	120	4.7
27332			0	50	2.0	3.0	.12	145	5.7
27333			0	100	3.9	3.0	.12	195	7.6
27334			1	60	2.3	4.0	.16	170	6.7
27335			1	100	3.9	4.0	.16	210	8.2

*Metric dimensions actual • Inch dimensions approximate

*Metric dimensions actual • Inch dimensions approximate

Surface resistance of handles is $10^6 \cdot 10^9$ Ohms

27922 Precision Chip Lifter - ESD Safe Blade CVM steel, hardened, corrosion resistant finish. Precision handle high quality plastic, Dissipative material.

Item	No.	mm	mm	mm	Inch	lbs.
27922	1	3.5	50	145	5.7	.07



278 TORX® Screwdriver, With Precision PicoFinish® ESD Safe Dissipative Handle Blade high alloy CVM steel. Handle manufactured from impact resistant, dissipative material. ESD standard IEC 61340-5-1.

Item					
No.	Size	mm	inch	mm	inch lbs.
27860	T1	40	1.6	120	4.7 .03
27861	T2	40	1.6	120	4.7 .03
27862	T3	40	1.6	120	4.7 .03
27863	T4	40	1.6	120	4.7 .03
27864	T5	40	1.6	120	4.7 .03
27865	T6	40	1.6	120	4.7 .03
27866	T7	40	1.6	120	4.7 .03
27867	T8	40	1.6	120	4.7 .03
27868	T9	50	2.0	145	5.7 .04
27869	T10	50	2.0	145	5.7 .04
27870	T15	60	2.4	170	6.7 .07
27871	T20	60	2.4	170	6.7 .07

*Metric dimensions actual • Inch dimensions approximate



277 Hex Inch Driver, With Precision PicoFinish® ESD Safe Dissipative Handle Blade high alloy CVM steel.

Item	No.	Inch	mm	Inch	Inch	Inch
27770	3/32	60	2.4	6.1	.16	.16
27771	7/64	60	2.4	6.1	.20	.20
27772	1/8	60	2.4	6.1	.20	.20
27773	9/64	60	2.4	6.1	.21	.24
27774	5/32	60	2.4	6.1	.22	.24
27775	3/16	60	2.4	6.1	.25	.28
27776	7/32	60	2.4	6.7	.30	.32
27777	1/4	60	2.4	6.7	.34	.36

*Metric dimensions actual • Inch dimensions approximate



275 Hex Inch Driver, With Precision PicoFinish® ESD Safe Dissipative Handle Blade high alloy CVM steel. Handle manufactured from impact resistant, dissipative material. ESD standard IEC 61340-5-1.

Item						
No.	Inch	mm	Inch	mm	Inch	mm
27550	0.028	40	1.6	120	4.7	
27551	0.035	40	1.6	120	4.7	
27552	0.05	40	1.6	120	4.7	
27557	1/16	50	2.0	145	5.7	
27554	5/64	50	2.0	145	5.7	
27558	3/32	50	2.0	160	6.3	
27559	7/64	60	2.4	170	6.7	
27560	1/8	60	2.4	170	6.7	


*Metric dimensions actual • Inch dimensions approximate



275 Hex Metric Driver, With Precision PicoFinish® ESD Safe Dissipative Handle

Item						
No.	mm	mm	inch	mm	inch	lbs.
27550	0.7	40	1.6	120	4.7	.02
27551	0.9	40	1.6	120	4.7	.02
27552	1.3	40	1.6	120	4.7	.03
27553	1.5	50	2.0	145	5.7	.03
27554	2.0	50	2.0	145	5.7	.04
27555	2.5	60	2.4	170	6.7	.05
27556	3.0	60	2.4	170	6.7	.05

*Metric dimensions actual • Inch dimensions approximate



277 Metric Nut Driver, With Precision ESD Safe Dissipative Handle Blade high alloy CVM steel. Hard chromed finished.

Item						
No.	mm	mm	Inch	mm	Inch	Inch
27780	1.5	60	2.4	140	2.5	3.0
27781	2.0	60	2.4	140	3.2	4.0
27782	2.5	60	2.4	140	4.0	4.0
27783	3.0	60	2.4	155	5.0	5.0
27784	3.5	60	2.4	155	5.3	6.0
27785	4.0	60	2.4	155	5.5	6.0
27786	4.5	60	2.4	155	6.2	7.0
27787	5.0	60	2.4	155	6.8	7.0
27788	5.5	60	2.4	170	7.6	8.0

*Metric dimensions actual • Inch dimensions approximate