



P4: M-386A

Customer No:	No:1
--------------	------



ITEM NO:	LENGTH" L	LENGTH" X
ADP-V4-03	915	895
ADP-V4-06	1830	1810



MARKING: E300060 兄 AWM 20276 80°C 30V VW-1 c兄 E300060

AWM I/II A 80°C 30V FT1 MSL DisplayPort Cable

* NTOE: All relevant materials are complied with RoHS directive .

5	PVC HOOD COLOR TRANSPARENT	H1BK01-0304T01		M304
4	MOLDED PVC BLACK	H1BF01-0304K09		M304
3	DISPLAYPORT 20PIN PLASTIC HOOD BLACK	A1BC17-1172K09		M1172
2	UL20276 [(30AWG(1/0.254CCS)*1Pair+AL+D+MY)*5Pcs+(30AWG(1/0.254CCS*4C)]+AL+D +AMA 85% BRAID, OD6.5mm, JACKET BLACK, DRAWING NO.EAMB3005P3004C-1146	H5DE13-0304K09	Xmm	M304
1	DISPLAYPORT 20PIN PLUG, GOLD FLASH ON CONTACTS & GOLD CONNECTOR, BLACK INSULATOR, TINPLATE, ASSEMBLY TYPE(IDXM-12X1132-115)	A1BC17-1172K09	2SET	M1172
No.	DESCRIPTION		Q'TY	Supplier

APPROVED				Cable Length Unless Other Spec.	
CHECKED	HU			Tolerances:	
DESIGNER	ZHU			0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm	
DRAWING	YN	Title	VESA Certified DisplayPort 1.4 Cable with Latch 3 FT		
DATE	16/AUG/23	ITEM NO.	ADP-V4-03		
		UNIT:mm			

1	REV.1 2023.06.05	MODIFY PLUG SR	2	REV.2 2023.08.16	MODIFY LENGTH
---	------------------	----------------	---	------------------	---------------