


P3: M-SR394A

P4: M-386A

Customer No: No:1



ITEM NO:	LENGTH*L	LENGTH*X
ADP-V4-03	915	895
ADP-V4-06	1830	1810

9P90-2	
P1	P2
1	12 RED
3	10 WHITE
2	11 SHIELD
4	9 RED
6	7 WHITE
5	8 SHIELD
7	6 RED
9	4 WHITE
8	5 SHIELD
10	3 RED
12	1 WHITE
11	2 SHIELD
13	13 WHITE
14	14 RED
15	15 RED
17	17 WHITE
16	16 SHIELD
18	18 YELLOW
19	19 ORANGE
SHIELD	SHIELD

MARKING: E300060 兄 AWM 20276 80°C 30V VW-1 c兄 E300060

AWM I/II A 80°C 30V FT1 MSL DisplayPort Cable

* NTOE: All relevant materials are complied with RoHS directive .

5	PVC HOOD COLOR TRANSPARENT	H1BK01-0304T01		M304
4	MOLDED PVC BLACK	H1BF01-0304K09		M304
3	DISPLAYPORT 20PIN PLASTIC HOOD BLACK	A1BC17-1172K09		M1172
2	UL20276 [(30AWG(1/0.254CCS)*1Pair+AL+D+HW)*5Pcs+(30AWG(1/0.254CCS*4C))+AL+D+AMA 85% BRAID, OD6.5mm, JACKET BLACK, DRAWING NO.EAAB3005P3004C-1146	H5DE13-0304K09	Xmm	M304
1	DISPLAYPORT 20PIN PLUG, GOLD FLASH ON CONTACTS & GOLD CONNECTOR, BLACK INSULATOR, TINPLATE, ASSEMBLY TYPE(IDXM-12X1132-115)	A1BC17-1172K09	2SET	M1172
No.	DESCRIPTION		Q'TY	Supplier

APPROVED		CompuCableUSA		Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm	
CHECKED	HU				
DESIGNER	ZHU				
DRAWING	YN				
DATE	16/AUG/23	Item	VESA Certified DisplayPort 1.4 Cable with Latch 6 FT		
		ITEM NO.	ADP-V4-06		
		UNIT:mm			

REV.1 2023.06.05 MODIFY PLUG SR REV.2 2023.08.16 MODIFY LENGTH