





Electrical Test:

1. 100%Test(Open ,short ,miss wire)
2. Contact Resistance: 5 ohm Max
3. Insulation Resistance: 10M ohm Min
4. Hi-Pot: 100V DC/10ms

Pin Assignment



						TOLERANCE						
						INCHES	M/M					
				.X	.015			.30	TITLE: VESA Certified DisplayPort 1.4 Cable with Latch 15 Feet			
				.XX	.010			.10				
				.XXX	.005			.05				
5	Inside Molding: LDPE			5	g		DRAWN BY		Chen Bin			
4	Outside Molding: 45P PVC			12	g		CHECK BY					
3	DisplayPort Port M ABS Shell Color: Black			2	pcs		APPD BY					
2	DisplayPort Port M Insulation Black Shell Gold Plated			2	pcs				CUSTOMER :			
1	DP1.4~[26AWG(7/0.16TC)+EAM]*5P+26AWG(7/0.16TC)*4C+AEB(16/11/0.12 85%AL)OD:8.5MM~Color: Black Marking:DisplayPort Cable E515987 1/2 AWM STYLE 20276 80°C 30V VW-1 C1			4.59	M				P/N:			
NO.	DESCRIPTION			Q'TY	UNIT			SCALE		NONE	DRAWING NO:	REV A0
								UNIT		MM		
								DATE		2023.04.12		