




MARKING: High Speed HDMI™ Cable E468039 (UL) CMP c(UL) 75°C 32/3C 28/3C 24/1C

* NOTE: All relevant materials are complied with RoHS directive .

9R02		
P1		P2
(GREEN) HPD	—————	HPD (GREEN)
(YELLOW) LY	—————	LY (YELLOW)
(WHITE) LX	—————	LX (WHITE)
(ORANGE) UTY	—————	UTY (ORANGE)
(BLUE) CEC	—————	CEC (BLUE)
(RED) VCC	—————	+5V (RED)
(BLACK+DRAIN) GND	—————	GND (BLACK+DRAIN)
(BROWN) TMDS0	FIBER(OM3)	TMDS0 (BROWN)
(GREEN) TMDS1	FIBER(OM3)	TMDS1 (GREEN)
(ORANGE) TMDS2	FIBER(OM3)	TMDS2 (ORANGE)
(BLUE) CLK	FIBER(OM3)	CLK (BLUE)

REV.2 2023.11.10	MODIFY HDMI19 MALE DESCRIBE	REV.3 2024.03.12	MODIFY HDMI 2.1 PICTURE
REV.1 2023.09.26	MODIFY BRIGHT GOLD AND PERFORMANCE PARAMETER	CHECKED	

7	JUMPER(1.12.03.00014)	A1KU02-1293	2PC	M1293
6	HOOD COLOR PVC TRANSPARENT	H1BK01-0304T01		M304
5	(50/125um FIBER*4C+MID)*1C+7/0.08Tx3C+7/0.127T*(2C+1C)+7/0.20Tx1C+F+D+AL OD:4.8 CMP (8K) JACKET BLACK,	A2PE03-0003K09	L-20mm	M3
4	HDMI 19 PIN ZN ALLOY HOOD AND SCREW AND WITH PAD, BRIGHT GOLD(Display 8K UHD Active Optical HDMI)	A6GC23-1295	1set	M1295
3	HDMI 19 PIN ZN ALLOY HOOD AND SCREW AND WITH PAD, BRIGHT GOLD(Source 8K UHD Active Optical HDMI)	A6GC24-1295	1set	M1295
2	HDMI19 MALE, GOLD FLASH ON CONTACTS & GOLD CONNECTOR, BLUE INSULATOR (FIBER+PCB+GREEN+AFA.H2312RXN-50, JUMPER:1.12.03.00014)	A1KK98-1293	1PC	M1293
1	HDMI19 MALE, GOLD FLASH ON CONTACTS & GOLD CONNECTOR, BLUE INSULATOR (AFA.H2312TXN-50, JUMPER:1.12.03.00014)	A1KK97-1293	1PC	M1293

No.	DESCRIPTION		Q'TY	Supplier
APPROVED		CompuCable^{USA}		
CHECKED	HU			
DESIGNER	ZHU	Product Title :	8K/UHD HDMI 2.1, Built-in Signal Booster, AOC, CMP, Type A to Type A, M/M, 35 FT to 150 FT	
DRAWING	PLS			
DATE	12/MAR/24	ITEM NO.		
			AHM8K60CMP-XX	
			UNIT:mm	

Cable Length Unless Other Spec.
 Tolerances:
 0 ~200mm ±10mm
 201~1000mm ±20mm
 1001 ~1500mm ±25mm
 1501~2100mm ±30mm
 2100mm↑ ±40mm