DREMEL



Dremel 4300-9/64

Model # 4300-9/64

Product Specifications

The Dremel 4300 is the first Dremel rotary tool to allow tool-less and collet-less accessory changes with the inclusion of the three-jaw chuck. The chuck accepts all Dremel accessory shank sizes for fast and convenient accessory changes without ever using a wrench. Featuring the all new Pivot Light, your projects are well-lit with an optimum line of sight since the light pivots to direct illumination where you want it. Experiencing the full range of Dremel rotary tool applications is easier than ever because the 4300 offers our most powerful motor with built-in variable speed and electronic feedback circuitry. And the slim, ergonomic body design provides a comfortable 360-degree grip zone no matter how you hold it for extended ease of use. The completely redesigned airflow system lets the Dremel 4300 run cool, quiet, and smooth so completing projects are more enjoyable than ever. Premium case included.

- Pivot light rotates to illuminate your project
- Universal 3-jaw chuck for easy accessory changes
- Quieter and cooler running due to improved air flow
- Our most powerful motor for maximum performance in demanding applications
- Compatible with all Dremel rotary tool attachments and accessories (*some applications require the use of a collet system, included in kit)
- Variable-speed with electronic feedback for consistent performance in all applications
- Separate on/off switch and speed control dial for added convenience between jobs
- Replaceable motor brushes extend tool life
- Cool-running ball bearing construction for smooth and quiet operation
- Industry leading customer support
- Two-year warranty

DIMENSIONS	
Speed:	Variable (5,000 - 35,000 RPM)
Contents:	Dremel 4300, Pivot Light, 225 Flex Shaft, A550 Shield, A577 Detailer's Grip, 678 Circle Cutter/Straight Edge Guide, 575 Right Angle, A576 Sanding/Grinding Guide, 565 Cutting Guide and 675 Garden Tool Sharpener
Warranty:	Limited 2 Years
Cord Length:	6[ft]
Length:	9["]
Voltage:	120V

Amperage:	1.8
Height:	2["]
Speed Range:	5,000 - 35,000 RPM
Width:	2["]
Weight:	1.175[kg, lb, oz]
Tool Level:	1 - Corded – variable speed high