

P1: M-Y084A		Customer No.: No.1	
M-O84A			
P2: M-O05B			

P1

NEMA 5-15P (MSL-105)

IEC 320 C13 (MSL-107)

P2

PACKING A: <3M

PACKING B: >3M

P1,P2: E210037-VN

NOTE: All relevant materials are complied with RoHS directive .
THE MARKING IS PROTRUDING LETTERING MOULD

CABLE MARKING:

(UL) SJT 3/C 18AWG(0.824MM²) VW-1 105°C 300V E204978 C(UL)

SJT 3/C 0.824MM² (18AWG) FT2 105°C 300V E204978 MSL-VN-

P1	P2
BLACK L	L
WHITE N	N
GREEN E	E

3	UL SJT 18AWG x 3C, OD 7.8mm, JACKET COLOR WHITE(RAL9001), DRAWING No. EPSVT011803C-142	H5TC20-0304W36	L-30mm	M304
2	MOLDED PVC 35P, COLOR WHITE(RAL9001)	H1BC02-0304W36		M304
	BRACKET: YS-003	A1QC14-0767	1	M767
	TERMINAL: 2*4mm, 98740BS-0/A	A1QB55-0257	3	M257
1	MOLDED PVC 35P, COLOR WHITE(RAL9001)	H1BC02-0304W36		M304
	TERMINAL WITH BRACKET: M87629LA-3PB	A1QC82-0257K09	1	M257
No.	DESCRIPTION		Q'TY	Supplier

APPROVED

CHECKED

DESIGNER

DRAWING

HU

JIANG

ZHU

Cable Length Unless Other Spec.
Tolerances:
0 ~200mm ±10mm
201~1000mm ±20mm
1001 ~1500mm ±25mm
1501~2100mm ±30mm
2100mm↑ ±40mm

DATE	10/NOV/21	ITEM NO.	AC-012XX-WH	UNIT:mm	
------	-----------	----------	-------------	---------	--

NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm