







P1: M-Y084A
M-084A
P2: M-005B

Customer No.: No.1



P1,P2: cULus E210037-VN

NOTE: All relevant materials are complied with RoHS directive .
THE MARKING IS PROTRUDING LETTERING MOULD

CABLE MARKING:

(UL) SJT 3/C 18AWG(0.824MM²) VW-1 105°C 300V E204978 c(UL)
SJT 3/C 0.824MM²(18AWG) FT2 105°C 300V E204978 MSL-VN-

P1	P2
BLACK L	L
WHITE N	N
GREEN E	E

3	UL SJT 18AWG x 3C, OD 7.3mm, JACKET COLOR BLUE(pantone 286c), DRAWING No. EPSVT011803C-142	H5TC20-0304U34	L-30mm	M304
2	MOLDED PVC 35P, COLOR BLUE(pantone 286c)	H1BC02-0304U34		M304
	BRACKET: YS-003	A1QC14-0767	1	M767
	TERMINAL: 2*4mm, 98740BS-0/A	A1QB55-0257	3	M257
1	MOLDED PVC 35P, COLOR BLUE(pantone 286c)	H1BC02-0304U34		M304
	TERMINAL WITH BRACKET: M87629LA-3PB	A1QC82-0257K09	1	M257
No.	DESCRIPTION		Q'TY	Supplier

APPROVED

CHECKED

DESIGNER

DRAWING

DATE

HU

JIANG

ZHU

10/NOV/21

ITEM NO.

CompuCableUSA

AC-012XX-BU

Cable Length
Unless Other Spec.
Tolerances:
0 ~200mm ±10mm
201~1000mm ±20mm
1001 ~1500mm ±25mm
1501~2100mm ±30mm
2100mm↑ ±40mm

UNIT:mm



NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm