

|               |      |
|---------------|------|
| Customer No.: | No.1 |
|---------------|------|



CABLE MARKING:

(UL) SJT 3/C 18AWG(0.824MM<sup>2</sup>) VW-1 105°C 300V E204978 C(UL)

SJT 3/C 0.824MM<sup>2</sup> (18AWG) FT2 105°C 300V E204978 MSL-VN-

|          |                                                                                             |                                                                                                                                                                                            |             |      |          |                                                                                       |
|----------|---------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|------|----------|---------------------------------------------------------------------------------------|
| 3        | UL SJT 18AWG x 3C, OD 7.8mm, JACKET COLOR GREEN(pantone 376c), DRAWING No. EPSVT011803C-142 | H5TC20-0304N28                                                                                                                                                                             | L=30mm      | M304 |          |                                                                                       |
| 2        | MOLDED PVC 35P, COLOR GREEN(pantone 376c)                                                   | H1BC02-0304N28                                                                                                                                                                             |             | M304 |          |                                                                                       |
|          | BRACKET: YS-003                                                                             | A1QC14-0767                                                                                                                                                                                | 1           | M767 |          |                                                                                       |
|          | TERMINAL: 2*4mm, 98740BS-0/A                                                                | A1QB55-0257                                                                                                                                                                                | 3           | M257 |          |                                                                                       |
| 1        | MOLDED PVC 35P, COLOR GREEN(pantone 376c)                                                   | H1BC02-0304N28                                                                                                                                                                             |             | M304 |          |                                                                                       |
|          | TERMINAL WITH BRACKET: M87629LA-3PB                                                         | A1QC82-0257K09                                                                                                                                                                             | 1           | M257 |          |                                                                                       |
| No.      | DESCRIPTION                                                                                 |                                                                                                                                                                                            |             | Q'TY | Supplier |                                                                                       |
| APPROVED |                                                                                             | <div>CompuCableUSA</div> <div>Cable Length Unless Other Spec.<br/>Tolerances:<br/>0 ~200mm ±10mm<br/>201~1000mm ±20mm<br/>1001 ~1500mm ±25mm<br/>1501~2100mm ±30mm<br/>2100mm↑ ±40mm</div> |             |      |          |                                                                                       |
| CHECKED  | HU                                                                                          |                                                                                                                                                                                            |             |      |          |                                                                                       |
| DESIGNER | JIANG                                                                                       |                                                                                                                                                                                            |             |      |          |                                                                                       |
| DRAWING  | ZHU                                                                                         |                                                                                                                                                                                            |             |      |          |                                                                                       |
| DATE     | 10/NOV/21                                                                                   | ITEM NO.                                                                                                                                                                                   | AC-012XX-GN |      | UNIT:mm  |  |