







P1:	M-Y084A
	M-084A
P2:	M-005B

Customer No.: No.1



PACKING B: >3M



P1,P2: cULus E210037-VN

NOTE: All relevant materials are complied with RoHS directive .
THE MARKING IS PROTRUDING LETTERING MOULD

CABLE MARKING:

(UL) SJT 3/C 18AWG(0.824MM²) VW-1 105°C 300V E204978 c(UL)
SJT 3/C 0.824MM²(18AWG) FT2 105°C 300V E204978 MSL-VN-

	P1		P2
BLACK	L	—————	L
WHITE	N	—————	N
GREEN	E	—————	E

3	UL SJT 18AWG x 3C, OD 7.3mm, JACKET COLOR RED(pantone 201c), DRAWING No. EPSYT011803C-142	H5TC20-0304R18	L-30mm	M304
2	MOLDED PVC 35P, COLOR RED(pantone 201c)	H1BC02-0304R18		M304
	BRACKET: YS-003	A1QC14-0767	1	M767
	TERMINAL: 2*4mm, 98740BS-0/A	A1QB55-0257	3	M257
1	MOLDED PVC 35P, COLOR RED(pantone 201c)	H1BC02-0304R18		M304
	TERMINAL WITH BRACKET: M87629LA-3PB	A1QC82-0257K09	1	M257
No.	DESCRIPTION		Q'TY	Supplier

APPROVED		CompuCableUSA		Cable Length Unless Other Spec. Tolerances:		
CHECKED	HU			0 ~200mm	±10mm	
DESIGNER	JIANG			201~1000mm	±20mm	
DRAWING	ZHU			1001 ~1500mm	±25mm	
				1501~2100mm	±30mm	
				2100mm↑	±40mm	
DATE	10/NOV/21	ITEM NO.	AC-012XX-RD		UNIT:mm	 

NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm