1.69.010.005/0000



TILTED DIAMOND⁺3 signal lamp, lamp red / yellow / green, 24 Volt, bezel transparent, M12 4-pin A-coded



fields of application

- > Measurement-control-regulation
- > Electrical engineering
- > Mechanical and system engineering
- > Signalling systems
- > Vehicle construction
- > Industrial robots
- > Model construction

description

> general

technical data

rc	GI	ш	IIC	aı	ua	LC

illuminated Yes

Bezel color transparent

Luminous element color red / yellow / green

Bezel shape convex Collar shape round -30 °C Operating temperature, min. Operating temperature, max. 60 °C -40 °C Storage temperature, min. 85 °C Storage temperature, max. Luminous elements **LED** Packaging Box Packaging unit 1 pcs. Degree of protection, front side, **IP66** according to DIN EN 60529 IP67

> mounting diameters

Mounting depth 14.5 mm
Installation height 70.1 mm
Outside dimension, width 56.8 mm
Collar dimension 56.8 mm

> mechanical data

Fixing Screw

Terminal on the rear M12 4-pin A-coded

PIN 1 LED red
PIN 2 LED green
PIN 3 GND

direct links

> RAFI eCatalog

The information in this data sheet only contains general descriptions and / or performance features, which may not apply precisely as described to the respective application, and which my change due to further product enhancements. The technical data, illustrations and other information about our products are the mere results of individual technical testing. These descriptions and other product features are only binding if they expressly agreed upon at the time of the conclusion of a binding contract. In all other cases, we reserve the right to make technical changes as well as changes of availability. Pictures and other graphic illustrations are approximations only. All product names may be trademarks or brand names of the RAFI Group or any other sub-supplier of RAFI. The use of such by any third parties for their own purposes may infringe the rights of the respective entity holding those rights.

date: Aug 16, 2019 page: 1/3

RAFI GmbH & Co. KG

Ravensburger Str. 128-134 88276 Berg / Ravensburg Germany www.rafi.de, info@rafi.de

1.69.010.005/0000



PIN 4 LED yellow

> electrical data

Rated operating voltage 24 V Operating voltage of the luminous 20 V

element, min.

Operating voltage of the luminous 28 V


element, max.

1.69.010.005/0000




drawings

System drawing



Mounting hole drawing



Schematic diagram

