


PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



SHELL	PART NUMBER	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07
09	D09S24A6GV146LF	30.81	24.99	16.96	16.21	10.96
15	D15S24A6GV146LF	39.14	33.32	25.18	24.54	19.18
25	D25S24A6GV146LF	53.03	47.04	39.12	38.25	33.12
37	D37S24A6GV146LF	69.32	63.50	55.68	54.71	49.68

Special code 146-0.76μ gold plated contacts

FOR ALL OTHER TECHNICAL CHARACTERISTICS:
SEE DRAWING C01-8646-0000

mat'l. code				surface	tolerance	projection	product family			
-				ISO 1302	ISO 406 ISO 1101		D-SUB			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title			
A	-	GREGAR	2016-14-12	angles	linear		DELTA-D STRAIGHT SPILL			
						MM	0.76μ GOLD PLATED CONTACTS			
				0°±2°		scale NTS	dwg no		sheet 1 of 1	size
				dr	GREGAR MATHEW	2016-14-12	10142204			A3
				engr	MITHUN PAUL	2016-14-12				
				chr	MITHUN PAUL	2016-14-12				
				appd	BIJU K PAUL	2016-14-12				
sheet index	revision sheet	A	1				type Product Customer Drawing			