

MATERIAL:

COMPOSITION: 98.25 - 98.75% LEAD 1.25 - 1.75% ANTIMONY

580°F SOLIDUS 600°F LIQUIDUS

(H)

												
	PART NUMBER	AMP RATING	DIA.	TOLERANCE ± .008 .0003		FEET PER LB.	SPOOL CONTAINS		TURNS ON SPOOL		SPOOL NO.	
	BFW 2/10	2/10	<u>.102</u> .0040			16350	250 FT.		675		7421	
	BFW 1/4	1/4	<u>.114</u> .0045			12920						
			. <u>127</u> .0050			10464						
	BFW 1/2	1/2	<u>.25</u> .010			2616	1/2	LB.			7788	
	BFW 3/4	3/4	<u>,33</u> ,013			1548						
	BFW 1	1	<u>.41</u> .016			1020				,	-	
L	BFW 1 1/2	1 1/2	<u>.51</u> .020	<u>.010</u> .0004		654						
L	BFW 2	2	<u>.64</u> .025	<u>.03</u> .001	(Ξ)	419						
	BFW 3	3	.79 .031	<u>.03</u> .001	(Ξ)	272						
	BFW 4	4	<u>.89</u> .035	<u>.05</u> .002	(Ξ)	213	1 1	_B.				
	BFW 5	5	<u>.99</u> .039	<u>.05</u> .002	(Ξ)	172						
	BFW 6	6	<u>1.07</u> .042	<u>.05</u> .002	Œ	148						
			4									