



## **Pan-Lug™ PCSB350-4-3 Multi-Tap Mechanical Connectors, Double Sided**

**PCSB350-4-3**

Multi-Tap connector, double-sided, clear insulation, 4 ports, 350 kcmil - #10 STR, #10 SOL.

### **Specifications**

Product Type	Double-Sided Multi-Tap Connector
Base Material	Aluminum
Insulation Material	Clear PVC
Number of Ports	4
Screw Type	Hex
Maximum Aluminum Conductor Size (kcmil)	350
Minimum Aluminum Conductor Size (AWG)	10
Maximum Copper Conductor Size (kcmil)	350
Minimum Copper Conductor Size (AWG SOL)	10
Overall Length (In.)	4.17
Overall Length (mm)	105.9
Overall Width (In.)	3
Overall Width (mm)	76.2
Overall Height (In.)	2.5
Overall Height (mm)	63.5
Standards Met	UL listed and CSA certified for use up to 600V & Temperature Rated to 90°C
CSA Temperature Rating (°C)	90
UL Temperature Rating (°C)	90
Maximum Voltage (V)	600
Note	For Use with Aluminum or Copper Code Conductors
Sub Brand	Pan-Lug™
Application	Aluminum or Copper Code Conductors
Part Features	Each port pre-filled with oxide inhibiting joint compound seals out air and moisture to deter surface oxidation.

**Packaging Detail**

UPC	07498377464
Std. Pkg. Qty.	3
Std. Pkg. Volume (cf)	0.1172
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000