# Vision HD Ultra Digital Focus

# ENPMZH611

The Energizer® VISION HD Ultra with Digital Focus delivers high-performance innovation with an exceptional light output brightness and hours of runtime. The Energizer patented Digital Focus technology allows consumers to choose their optimal array of light between focused and area light by simply pressing the light switch. Unique MAXVIZ technology enables users to experience sharp, high-definition performance with daylight color and wide, uniform light output. This new light is our brightness light with 1500 Lumens and with its aircraft grade aluminum, it delivers exceptional quality and durability. The Energizer Vision HD Ultra is dependable and perfect for indoor situations such as DIY project and power outages, as well as outdoor activities such as camping.



Provides 1500 Lumens of Light



Provides Run Time of 4 Hours



Sustains 1 Meter Drop Test.



Illuminates objects up to 230m away.



Water Resistant IPX4 – works after splashing water on all sides

#### **DESIGN BENEFITS**

- ✓ Durable Aircraft Grade Aluminum
- ✓ One handed focusing operation: Digital Focus
- ✓ Versatility: multiple modes
- ✓ 20 Years Design to Last based on typical consumer usage patterns
- Strobe mode: hold switch for 2 seconds to activate
- ✓ Shatterproof Lens

## LIGHT AND POWER SOURCE

- ✓ Features LED Technology
- √ 4.25 Hz strobe light
- ✓ Operates on 6 AA Batteries

#### **ELECTRICAL CHARACTERISTICS**

Electrical Characteristics Nominal Power: Power consumption 11.4W / Batteries AA Energizer E91 4.5V dc

LED Specifications: LED 3.0V cc / 3800 mA

### **CERTIFICATES AND COMPLIANCE**

C ∈ RoHS

EMC, EN62471, FCC



This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Tested according to ANSI/NEMA FL1 Standards.

Results based on: Energizer MAX Alk / E91

#### PERFORMANCE BENEFITS

- ✓ Up to 15X Brighter than Standard LED Technology
- ✓ Long Run Time
- MAXVIZ Technology to deliver a wide, powerful beam and high-definition vision

#### SPECIFICATIONS

Weight Excluding Batteries:

278 Grams / 9.81 Ounces

**Dimensions:** 

226mm x 48mm / 35mm or 8.88" x 1.88" / 1.38"

#### NUMBER OF OPERATING MODES: 7

NOWIDER OF OPERATING WIODES. 7				
Lumens	Runtime (h)	Beam Distance (m)		
1500	4	230		
250	15	-		
-	-	-		
Digital Focus				
			Lumens 1500	Lumens Runtime (h)  1500 4  250 15

Before using your flashlight, please read all instructions and cautionary marking on the package and the light.