


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF EASE ELECTRONICS. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF EASE ELECTRONICS IS PROHIBITED.

REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/6/25	CHILLY. L



UNIT: MM

Part Number Table

PART NUMBER	DESCRIPTION	DWG. NO.
9134543J0070	RJ45 Strain Relief Boot, Black	J0070
9134544J0071	RJ45 Strain Relief Boot, Blue	J0071
9134545J0072	RJ45 Strain Relief Boot, Green	J0072
9134546J0073	RJ45 Strain Relief Boot, Gray	J0073
9134547J0074	RJ45 Strain Relief Boot, Orange	J0074
9134548J0075	RJ45 Strain Relief Boot, Purple	J0075
9134549J0076	RJ45 Strain Relief Boot, Red	J0076
9134550J0077	RJ45 Strain Relief Boot, White	J0077
9134551J0078	RJ45 Strain Relief Boot, Yellow	J0078

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15 PROJECTION 	APPROVALS	DATE	<div>EASE</div> <div>electronics</div> <div>Ease Electronics Co., Limited</div> <div>Zone A, 2nd Floor, Bldg A, No.45, Qianjin 3rd Rd, Tanzhou, 528467</div> <div>Zhongshan, Guangdong, China. +86-756-58 8881 0</div>			
	DRAWN BY LUKE. L	6/6/2025				PART NUMBER 9134549J0076
	CHECKED BY TILLY. H	6/6/2025				
	APPROVED BY CHILLY. L	7/6/2025				
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION RJ45 Strain Relief Boot, Red		ID	SERIES NO.	DWG. NO.	REV.
			J	RJ45-B	J0076	J
			REF	SCALE: NONE	CAD FILE: J0076	SHEET 1 OF 1