





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN15C0509~513	2015/12/21	Vicky	Update Logo & Note



BD-08BFFM-SL7AXX
 ↑
 XX:01~99Meter
 01:01Meter
 02:02Meters
 ∴
 99:99Meters
 Cable Length(L):01~99Meters



- Note:
- * @C Important Dimension To Check.
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF, Black
 - * Female Pin: Copper Alloy, Gold Plated
 - * Cable: UL2464 24AWG*8C+D+Al/My, PVC Jacket, UV Resistant, OD=5.5mm, Black
 - * Cable Length Tolerance: 01M:±40mm
 02M~05M:±60mm
 06M~10M:±100mm
 11M~30M:±200mm
 31M~99M:±500mm



Pin Assignments
Front View

8	Green	綠
7	Yellow	黃
6	Orange	橘
5	Red	紅
4	Blue	藍
3	White	白
2	Brown	棕
1	Black	黑
Conn.	Wire Color	

UNIT:mm	
TOLERANCE	±0.5 mm

TITLE	Standard Cable Screw 8Pin F Conn F Pin	
SCALE	Free	SHEET 1 OF 1
REV.	B	SIZE A4 @C :Inspection Item

Amphenol LTW
 安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE
	Vicky	2015/12/21
BD-08BFFM-SL7AXX	Rita	2015/12/21
ALTW	Lisa	2015/12/21

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

F
E
D
C
B
A

1 2 3 4 5 6 7 8