

6

5

4


3

2

1

D

D




10.72±0.25 [.422±.010]

5.92±0.13 [.233±.005]

0.91±0.20 [.036±.008]

11.10 [.437] MAX.




C

C

B

B





A

A

**NOTES:**

- MATERIAL AND FINISHES:  
INSULATOR: GLASS FILLED PBT POLYESTER, UL 94V-0. COLOR: BLACK.  
SHELLS: STEEL, ZINC PLATE WITH CHROMATE SEAL.
- DETAILED PRODUCT, MECHANICAL AND ELECTRICAL INFORMATION IS AVAILABLE IN THE LATEST STANDARD DENSITY D-SUB PRODUCT PUBLICATION AT [CONNECTPOSITRONIC.COM](http://CONNECTPOSITRONIC.COM)

BY	ND	CHK	SS	3RD ANGLE	POSITRONIC BELIEVES THE DATA ON THE DRAWING TO BE RELIABLE. THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.		 <b>Positronic®</b> CONNECT POSITRONIC.COM
APR	SS	RELEASED DATE: 2022-10-02					
TOLERANCES				SCALE			
±0.03mm [.001 INCHES] FOR MALE CONTACT MATING DIAMETERS ±0.08mm [.003 INCHES] FOR CONTACT TERMINATION DIAMETERS ±0.13mm [.005 INCHES] FOR ALL OTHER DIAMETERS ±0.38mm [.015 INCHES] FOR ALL OTHER DIMENSIONS ±5° FOR ALL ANGLES DIMENSION ARE IN MILLIMETERS [INCHES]				NTS			
				PART NUMBER	SD15M00000		SERIES
							SD
				TITLE	SD15M00000		
CREATED ON:				SHEET	SHEET 1 OF 1		REV
2022-10-02							A

6

5

4

3

2

1