

6

5


4

3

2

1

D



C


10.90±0.25 [.429±.010]

6.17±0.13 [.243±.005]


0.91±0.20 [.036±.008]

11.10 [.437]
MAX.

D



B



C

B

A

NOTES:

- MATERIAL AND FINISHES:**
INSULATOR: GLASS FILLED PBT POLYESTER, UL 94V-0. COLOR: BLACK.
SHELLS: STEEL, ZINC PLATE WITH CHROMATE SEAL.
- DETAILED PRODUCT, MECHANICAL AND ELECTRICAL INFORMATION IS AVAILABLE IN THE LATEST STANDARD DENSITY D-SUB PRODUCT PUBLICATION AT CONNECTPOSITRONIC.COM

6

5

4

3

2

1

A

BY NVP	CHK ND	3RD ANGLE 	POSITRONIC BELIEVES THE DATA ON THE DRAWING TO BE RELIABLE. THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.	
APR SS	RELEASED DATE: 2022-10-02	SCALE NTS		
TOLERANCES ±0.03mm [.001 INCHES] FOR MALE CONTACT MATING DIAMETERS ±0.08mm [.003 INCHES] FOR CONTACT TERMINATION DIAMETERS ±0.13mm [.005 INCHES] FOR ALL OTHER DIAMETERS ±0.38mm [.015 INCHES] FOR ALL OTHER DIMENSIONS ±5° FOR ALL ANGLES DIMENSION ARE IN MILLIMETERS [INCHES]				
PART NUMBER SD50F00000			SERIES SD	
TITLE SD50F00000				
CREATED ON: 2022-10-02	SHEET SHEET 1 OF 1	REV A		