

6

5

4

3

2

1

D

D

C


C

B

B

A

A

**NOTES:****1. MATERIALS AND FINISH:**

INSULATOR: GLASS FILLED PBT POLYESTER, UL 94V-0, COLOR: BLACK.
 CONTACTS: PRECISION MACHINED COPPER ALLOY, GOLD FLASH OVER NICKEL PLATE.
 SHELLS: STEEL, ZINC PLATED.
 HOOD AND HOOD COVER: GLASS FILLED POLYESTER, UL 94V-0, COLOR: BLACK.
 LOCK LEVER AND CABLE CLAMPS: STEEL, NICKEL PLATE.
 LOCK ARM SPRING: BERYLLIUM COPPER, NICKEL PLATE.
 CABLE CLAMP SCREWS: BRASS, ZINC PLATED.
 COVER SCREWS AND MOUNTING SCREWS: STEEL, ZINC PLATED.

- 2. DETAILED PRODUCT, MECHANICAL AND ELECTRICAL INFORMATION IS AVAILABLE IN THE LATEST STANDARD DENSITY D-SUB PRODUCT PUBLICATION AT CONNECTPOSITRONIC.COM.**
- 3. CRIMPING TOOL INFORMATION IS AVAILABLE AT WWW.CONNECTPOSITRONIC.COM/CrimpToolCrosslist.**

BY KKP	CHK AP	3RD ANGLE 	POSITRONIC BELIEVES THE DATA ON THE DRAWING TO BE RELIABLE. THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.	
APR AB	RELEASED DATE: 2025-04-16	SCALE NTS		
TOLERANCES ±0.03mm [0.001 INCHES] FOR MALE CONTACT MATING DIAMETERS ±0.08mm [0.003 INCHES] FOR CONTACT TERMINATION DIAMETERS ±0.13mm [0.005 INCHES] FOR ALL OTHER DIAMETERS ±0.38mm [0.015 INCHES] FOR ALL OTHER DIMENSIONS ±5° FOR ALL ANGLES DIMENSION ARE IN MILLIMETERS [INCHES]			PART NUMBER SD9M10JVL0	SERIES SD
CREATED ON: 2025-04-15			SHEET SHEET 1 OF 1	REV A

6

5

4

3

2

1