




Rating	25A 14VDC
Contact Resistance	50m ohm Max.
Insulation Resistance	DC 500V 100M ohm Min.
Dielectric Strength	AC 1500V 1 minute
Operation Temp.	- 25° C ~ 85° C
Switch Function	3P SPST ON - OFF (LED)

Mounting Hole			Circuit Diagram
Thickness	X	Y	
0.75....2.5	27.6-0.1	13.8+0.1	
2.5....3.5	27.8-0.1	13.8+0.1	
3.5....4.5	28.0-0.1	13.8+0.1	



***MATERIAL:**

Frame: Black, Nylon 66 (94-V2).
 Actuator: Red, PC Clear (94-V2).
 LED: Red.
 Waterproof Rubber: Black, Silicone.
 Terminals 1, 2: Silver plated, Copper alloy.
 Terminal 3: Brass alloy.
 Printed: None
 IP Rating: IP65



RoHS Compliant

1 Added Led: Red to Material Notes. 1/12/11

CW INDUSTRIES
 Southampton, Pa. 18966
 Tel 215.355.7080/www.cwind.com

Date Drawn: 1/12/11

Rev. 1

Unit: mm

Checked By: G.Guld

Title: **ROCKER SWITCH**

CW P/N: **GRB238B801BR1**