





THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

Rating	20A 125V AC	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm max.		
Insulation Resistance	DC 500V 100M ohm min.		SPST ON - OFF (ILLUMINATED)
Dielectric Strength	AC 1500V 1 minute		
Operating Temperature	-25 °C ~ 85 °C		
Switch Function	3P SPST ON-OFF (Illuminated)		

Cut-Out 1.0 ~ 3.0 mm thk.

MATERIAL:
Frame: Nylon 66 (94 V-2), Black
Actuator: PC (94 V-2), Red
Terminals: Silver plated Copper alloy.



RoHS Compliant	1				Removed 16A 250V AC from rating.	
 INDUSTRIES Southampton, Pa. 18966 Tel 215.355.7080/www.cwind.com	Date Drawn: 12/21/09		Rev. 1	Unit: mm	Checked By: G.Guld	
	Title: ROCKER SWITCH			CW P/N: GRB293B01BR		