

## Synthetic cable glands Syntec® with lamellar technology



### Entry thread NPT

#### Type approval: SYNTEC

- Black RAL 9005
- One-piece sealing ring

<b>Order number:</b>	<b>1545.N1000.22</b>
E-No:	121758629
EAN:	7611614078434
Material	Polyamide PA 6
Properties	halogen-free, black UV resistant (tested according to EN ISO 4892-2)
Sealing ring	CR (neoprene)
Operation temperature	-30°C / +100°C
Protection class	IP 54
Entry thread	NPT 1"
NEMA Type rating	4X
Clamping range min.	17.0 mm
Clamping range max.	22.0 mm
Wrench size	42 mm
Dimension H	36 mm
Thread length L	15 mm
UL - clamping range	19.5-22.0 mm
Dispatch	20