

Synthetic cable glands Syntec® with lamellar technology



Entry thread Pg

Type approval: SYNTEC

- Light grey RAL 7035
- One-piece sealing ring

Order number:	1555.16.11
E-No:	121755419
EAN:	7611614077826
Material	Polyamide PA 6
Properties	halogen-free, black UV resistant (tested according to EN ISO 4892-2)
Sealing ring	CR (neoprene)
Operation temperature	-30°C / +100°C
Protection class	IP 68
NEMA Type rating	4X
Entry thread	Pg 16
Clamping range min.	5.0 mm
Clamping range max.	11.0 mm
Wrench size	27 mm
Dimension H	30 mm
Thread length L	10 mm
UL - clamping range	6.5-11.0 mm
Dispatch	50