

Synthetic cable glands Syntec® with lamellar technology



Entry thread Pg

Type approval: SYNTEC

- Light grey RAL 7035
- One-piece sealing ring

Order number:	1555.48.44
E-No:	121754828
EAN:	7611614077895
Material	Polyamide PA 6
Properties	halogen-free, black UV resistant (tested according to EN ISO 4892-2)
Sealing ring	CR (neoprene)
Operation temperature	-30°C / +100°C
Protection class	IP 68
NEMA Type rating	4X
Entry thread	Pg 48
Clamping range min.	32.0 mm
Clamping range max.	44.0 mm
Wrench size	65 mm
Dimension H	48 mm
Thread length L	15 mm
UL - clamping range	44.0-44.0 mm
Dispatch	5