

Synthetic cable glands Syntec® with lamellar technology



Entry thread NPT

Type approval: SYNTEC

- Light grey RAL 7035
- One-piece sealing ring

Order number:	1555.N0750.14
E-No:	121759519
EAN:	7611614078076
Material	Polyamide PA 6
Properties	halogen-free, black UV resistant (tested according to EN ISO 4892-2)
Sealing ring	CR (neoprene)
Operation temperature	-30°C / +100°C
Protection class	IP 54
Entry thread	NPT 3/4"
NEMA Type rating	4X
Clamping range min.	6.5 mm
Clamping range max.	14.0 mm
Wrench size	33 mm
Dimension H	35 mm
Thread length L	15 mm
UL - clamping range	14.0-14.0 mm
Dispatch	25