

Synthetic cable glands Progress® GFK



Entry thread Pg

- Light grey RAL 7035
- One-piece sealing insert

Order number:	1571.11.120
EAN:	7611614137988
Material	Polyamide glass fiber reinforced
Properties	halogen-free
Seal	TPE
Operation temperature	-20°C / +100°C
Protection class	IP 68
Entry thread	Pg 11
Clamping range without insert min.	8.5 mm
Clamping range without insert max.	12.0 mm
Wrench size	24 mm
Dimension H	28 mm
Thread length L	12 mm
Dispatch	50