


Synthetic Syntec® cable glands with lamellar technology and anti-kink nozzle



Short entry thread metric

Type approval: SYNTEC mit Knickschutz

- Light grey RAL 7035
- One-piece sealing ring

Order number:	1576.12.06
E-No:	121784419
EAN:	7611614078878
Material	Polyamide PA 6
Properties	halogen-free, black UV resistant (tested according to EN ISO 4892-2)
Sealing ring	CR (neoprene)
Operation temperature	-30°C / +100°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68
NEMA Type rating	4X
Entry thread	M12x1.5
Clamping range min.	2.5 mm
Clamping range max.	6.5 mm
Wrench size	15 mm
Dimension H	54 mm
Thread length L	6 mm
UL - clamping range	5.0-6.5 mm
Dispatch	50