


Synthetic Syntec® cable glands with lamellar technology and anti-kink nozzle



Entry thread Pg

Type approval: SYNTEC mit Knickschutz

- Light grey RAL 7035
- One-piece sealing ring

Order number:	1576.13.12
E-No:	121781308
EAN:	7611614007205
Material	Polyamide PA 6
Properties	halogen-free, black UV resistant (tested according to EN ISO 4892-2)
Sealing ring	CR (neoprene)
Operation temperature	-30°C / +100°C
Protection class	IP 68
NEMA Type rating	4X
Entry thread	Pg 13
Clamping range min.	5.5 mm
Clamping range max.	12.0 mm
Wrench size	24 mm
Dimension H	88 mm
Thread length L	9 mm
UL - clamping range	9.5-12.0 mm
Dispatch	50