

90° elbow conduit connectors nickel-plated brass



90° elbow conduit connectors nickel-plated brass

- 90° elbow conduit connectors nickel-plated brass
- Short entry thread Pg

Order number:	5000.07.10
EAN:	7611614147376
Material	Nickel-plated brass
Seal	TPE
O-ring	To be ordered separately
Protection class	IP 40 - IP 66, in dependence of the combination of conduit and connector
Operation temperature	-40°C / +125°C
Outer diameter	10 mm
Entry thread	Pg 7
Dimension A	11 mm
Dimension B	32 mm
Dimension H	21 mm
Dimension L	8 mm
Wrench size	17 mm
Dispatch	50

Depending on the type of conduit, the stabilising bush must be ordered separately.