

Complete conduit gland nickel-plated brass



Complete conduit gland nickel-plated brass

- Conduit gland US-M
- FLEXAgraff®-SI-ASF

Order number:	5010.337.012
E-No:	126464320
EAN:	7611614117812
Material	Nickel-plated brass
Bushing	Polished brass
Sealing ring	TPE
O-ring	NBR
Properties	Highly watertight and dustproof, friction locking of conduit and gland, covered conduit ends, resistant to stretch and vibrations
Protection class	IP 67
Operation temperature	-40°C / +125°C
Outer diameter	14 mm
Entry thread	M12x1.5
Diameter Ø I	9.0 mm
Diameter Ø B	23 mm
Dimension C	10 mm
Dimension D	33 mm
Wrench size	19/21 mm
Dispatch	50

The reliability is only guaranteed with the corresponding stabilizing bush