



Klemsan®

551014 KKC 4060

40x60 Slotted wiring duct,Grey

General Product Information	Insulating material	PVC - UL 94 V0
Operating Temperature	Minimum Temperature	-15°C
	Maximum Temperature	+60°C
Dimensions	A	40 mm
	B	60 mm
	C	13,6 mm
	D	4 mm
	E	6 mm
	F	2,1 mm
	G	4,5 mm
	H	6,5 mm
	I	25 mm
Length	U	2 Mt.
Product Information	Packing Unit	12x2
	Working range	



UL Sertifikası - UL Certificate

Alçak Gerilim direktiflerine uygunluk belgesi - VDE Certificate

Rusya Yangın Sertifikası - Rusya Yangın Sertifikası

Ukrayna Uygunluk Sertifikası - Ukrayna Uygunluk Sertifikası

Avrupa standartlarına uygunluk belgesi - CE Certificate

Türk Standartlarına Uygunluk Belgesi - Wiring Duct TSE certificate

Order Info		Dimensions
	551014 40x60	40x60 Slotted wiring duct,Grey
	551014WS	40x60 Wide slotted wiring duct,Grey