



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF EASE ELECTRONICS. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF EASE ELECTRONICS IS PROHIBITED.

REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	18/6/25	CHILLY. L



MATERIAL

Surface Mounting Box: ABS
 Jack Housing: ABS
 Spring Pin: Phosphor Bronze, T=0.3mm, 50u" Gold over 120u" Matte Tin over 60u" Nickel undercoat
 Pin Holder: PBT
 PCB: FR-4
 IDC Housing: PC
 IDC Contact: Phosphor Bronze, T=0.4mm, 200u" Matte Tin over 100u" soft Nickel undercoat

Physical Characteristics

Insert Life: 750 mating cycles
 Contact Force: 100 grams
 Plug Retention Force: 11 lbf min
 Durability: 200 termination cycles
 Contact Compatibility: Accommodates 22 to 26 AWG solid / 24 AWG Stranded
 Operating Temperature Range: -10 °C to 60 °C
 Storage Temperature Range: -40 °C to 68 °C
 Humidity: 10% ~ 90% RH

ELECTRICAL

Insulation Resistance: 500 mΩ
 Dielectric Withstanding Voltage: 1000 V
 DC Current Rating: 1.5 Amps
 DC Resistance: 0.1 Ω
 Contact Resistance: 20 mΩ

Mounting Type: Patch Panel, Faceplates/Wall Plates, Surface Mount Boxes

UNIT: MM

Part Number Table

PART NUMBER	DESCRIPTION	DWG. NO.
RJ45-5JUT-BK	Cat.5e Toolless Keystone Jack Unshielded, Black	J0119
RJ45-5JUT-BL	Cat.5e Toolless Keystone Jack Unshielded, Blue	J0120
RJ45-5JUT-GN	Cat.5e Toolless Keystone Jack Unshielded, Green	J0121
RJ45-5JUT-GY	Cat.5e Toolless Keystone Jack Unshielded, Gray	J0122
RJ45-5JUT-IV	Cat.5e Toolless Keystone Jack Unshielded, Ivory	J0123
RJ45-5JUT-OR	Cat.5e Toolless Keystone Jack Unshielded, Orange	J0124
RJ45-5JUT-RD	Cat.5e Toolless Keystone Jack Unshielded, Red	J0125
RJ45-5JUT-WT	Cat.5e Toolless Keystone Jack Unshielded, White	J0126
RJ45-5JUT-YW	Cat.5e Toolless Keystone Jack Unshielded, Yellow	J0127

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15 PROJECTION 	APPROVALS	DATE	 Zone A, 2nd Floor, Bldg A, No.45, Qianjin 3rd Rd, Tanzhou, 528467 Zhongshan, Guangdong, China. +86-756-5888810 PART NUMBER <h2 style="text-align: center;">RJ45-5JUT-OR</h2> PRODUCT DESCRIPTION <h3 style="text-align: center;">Cat.5e Toolless Keystone Jack Unshielded, Orange</h3>
	DRAWN BY LUKE. L	17/6/2025	
	CHECKED BY TILLY. H	17/6/2025	
	APPROVED BY CHILLY. L	18/6/2025	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	ID J SERIES NO. RJ45-J DWG. NO. J0124 REV. J SCALE: NONE CAD FILE: J0124 SHEET 1 OF 1		