



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF EASE ELECTRONICS. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF EASE ELECTRONICS IS PROHIBITED.

REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	18/6/25	CHILLY. L



MATERIAL

Surface Mounting Box: ABS

Jack Housing: ABS

Spring Pin: Phosphor Bronze, T=0.3mm, 50u" Gold over 120u" Matte Tin over 60u" Nickel undercoat

Pin Holder: PBT

PCB: FR-4

IDC Housing: PC

IDC Contact: Phosphor Bronze, T=0.4mm, 200u" Matte Tin over 100u" soft Nickel undercoat

Physical Characteristics

Insert Life: 750 mating cycles

Contact Force: 100 grams

Plug Retention Force: 11 lbf min

Durability: 200 termination cycles

Contact Compatibility: Accommodates 22 to 26 AWG solid / 24 AWG Stranded

Operating Temperature Range: -10 °C to 60 °C

Storage Temperature Range: -40 °C to 68 °C

Humidity: 10% ~ 90% RH

ELECTRICAL

Insulation Resistance: 500 mΩ

Dielectric Withstanding Voltage: 1000 V

DC Current Rating: 1.5 Amps

DC Resistance: 0.1 Ω

Contact Resistance: 20 mΩ

Mounting Type: Patch Panel, Faceplates/Wall Plates, Surface Mount Boxes

UNIT: MM

Part Number Table

PART NUMBER	DESCRIPTION	DWG. NO.
RJ45-5JUT-BK	Cat.5e Toolless Keystone Jack Unshielded, Black	J0119
RJ45-5JUT-BL	Cat.5e Toolless Keystone Jack Unshielded, Blue	J0120
RJ45-5JUT-GN	Cat.5e Toolless Keystone Jack Unshielded, Green	J0121
RJ45-5JUT-GY	Cat.5e Toolless Keystone Jack Unshielded, Gray	J0122
RJ45-5JUT-IV	Cat.5e Toolless Keystone Jack Unshielded, Ivory	J0123
RJ45-5JUT-OR	Cat.5e Toolless Keystone Jack Unshielded, Orange	J0124
RJ45-5JUT-RD	Cat.5e Toolless Keystone Jack Unshielded, Red	J0125
RJ45-5JUT-WT	Cat.5e Toolless Keystone Jack Unshielded, White	J0126
RJ45-5JUT-YW	Cat.5e Toolless Keystone Jack Unshielded, Yellow	J0127

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15 PROJECTION 	APPROVALS	DATE	EASE Ease Electronics Co., Limited Zone A, 2nd Floor, Bldg A, No.45, Qianjin 3rd Rd, Tanzhou, 528467 Zhongshan, Guangdong, China. +86-756-58 8881 0	
	DRAWN BY LUKE. L	17/6/2025		
	CHECKED BY TILLY. H	17/6/2025	PART NUMBER RJ45-5JUT-WT	
	APPROVED BY CHILLY. L	18/6/2025	PRODUCT DESCRIPTION Cat.5e Toolless Keystone Jack Unshielded, White	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR		ID J	SHEET 1 OF 1
	REF		SCALE: NONE	CAD FILE: J0126