










 M12S-XXPMMS-SF8002
XX:No. Of Pin



- Note:
- * RoHS Compliant
 - *  Important dimension
 - * Waterproof rate: IP68, unmated 1m/24h
 IP69K, mated
 - * Connector Housing: Thermoplastic, Black
 - * Pin: Copper alloy, Gold plated
 - * Shield: Metal
 - * Nut: Metal
 - * O-Ring: Rubber, Black
 - * For panel thickness max: 4.5mm
 - * Nut is packed separately in pe bag

UNIT:mm			
TOLERANCE			
.X	±0.25		
.XX	±0.1		
.XXX	±0.05		
ANGLES	±1°		

TITLE N SEN, M12 S, SCREW RECEPTACLE, M, M, SOLDER			
SCALE 2:1	SIZE A4	SHEET 1 OF 1	
REV. C	WC-REV. .0	 :Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO 	DRAWN BY JC Chen	DATE 2023-02-09
DWG NO M12S-XXPMMS-SF8002	CHECKED BY Feng Li	DATE 2023-02-09
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2023-02-09

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.