



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A		2022/10/25	Yuwei Chou	Change Rev.03 To Rev.A
B	C221973	2022/12/26	Ruru	 X2






Recommended
Panel Cut-Out




雷射印字工單後6碼
字高: 0.93、字型: 新羅馬體

雷射印字: SUS
字高: 0.93、字型: 新羅馬體




- Note:
- * RoHS Compliant
 - *  Important dimension
 - *  Waterproof rate: IP68, unmated 1m/24h
 - * Connector
 - * Housing: Thermoplastic, Black
 - * Pin: Copper alloy, Gold plated
 - * Shield: Metal
 - * Nut: Metal
 - * O-Ring: Rubber, Green
 - * For panel thickness: 2.0~4.0mm
 - * Nut is packed separately in pe bag

SM8-XXPMMS-SF8001
XX: No. Of Pin



3P



4P

Pin Assignments Front View

UNIT:mm			TITLE N SEN, SM8-STAINLESS, SCREW RECEPTACLE, M, M, SOLDER 			
TOLERANCE			SCALE	SIZE	SHEET	OF
.X ±0.25			Free	A4	1	1
.XX ±0.1			REV.	WC-REV.		
.XXX ±0.05			B	A.1	 : Inspection item	
ANGLES ±1°						

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Yuwei Chou	2022/10/25
DWG NO	CHECKED BY	DATE
SM8-XXPMMS-SF8001	Aric Ko	2022/10/25
CUSTOMER	APPROVED BY	DATE
ALTW	Max Yang	2022/07/15