




D

C


B

A



プリント基板取付穴寸法図
(MOUNTING DIMENSIONS FOR P.C.BOARD)

- 1. 板厚, 1.6±0.15 (P.C.B. THICKNESS, 1.6±0.15)
- 2. 公差, ±0.1 (TOLERANCE, ±0.1)



注記:

- ① 面より2mmの範囲で測定のこと。
- ② 相手ハウジングと所定の機能を満たしてかん合できること。
- ③ フードの反りは0.2以内。
- 4 推奨取付けねじ; JIS B 1115 又は、1122 タッピンねじ
なべ1種又は2種、呼び径3長さ6mm以下
(締め付けトルク: 39.2N・m 以下)
- 5 適用製品規格; 108-5093
- 6 相手ハウジングとのかん合力は、29.4N以下
但し、リセプタクルコンタクトは含まない。

NOTES;

- ① TO BE MEASURED WITHIN 2mm FROM 面
- ② IN COUPLING WITH THE PLUG HOUSING MATING SATISFIES FUNCTION
- ③ WARPAGE 0.2 MAX.
- 4 RECOMMENDED MOUNTING SCREW; 3mmDIA, 6mmLENGTH(MAX.)
PAN HEAD, CLASS 1 AND 2 TAPPING SCREW SPECIFIED IN JIS B1115, B1122 (TIGHTENING TORQUE; 39.2N・cmMAX.)
- 5 SPEC. No. 108-5093
- 6 IN COUPLING WITH THE PLUG HOUSING MATING FORCE
29.4N MAX WITHOUT RECEPTACLE CONTACT

	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.38μ m MIN.)	NATURAL	2-5171894-1
	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.76μ m MIN.)	NATURAL	1-5171894-1
OBSOLETE	TIN-LEAD	SELECTIVE GOLD (0.38μ m MIN.)	GREEN	2-171894-4
OBSOLETE	TIN-LEAD	SELECTIVE GOLD (0.38μ m MIN.)	NATURAL	2-171894-1
OBSOLETE	TIN-LEAD	SELECTIVE GOLD (0.76μ m MIN.)	GREEN	1-171894-4
OBSOLETE	TIN-LEAD	SELECTIVE GOLD (0.76μ m MIN.)	NATURAL	1-171894-1
	PRE-TIN		YELLOW	171894-7
	PRE-TIN		GRAY	171894-6
	PRE-TIN		BLUE	171894-5
	PRE-TIN		GREEN	171894-4
	PRE-TIN		BROWN	171894-3
	PRE-TIN		BLACK	171894-2
	PRE-TIN		NATURAL	171894-1
	SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	COLOR 色	PART NUMBER 製品型番
	CONTACT FINISH コンタクト仕上			

TOLERANCE UNLESS OTHERWISE SPECIFIED: 一般公差
0<≦ 10 : ±0.2
10<≦ 30 : ±0.25
30<≦ 100 : ±0.3
ANGLE : ±3°
角度

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 桁
mm

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

MATERIAL
材料

HSG: 66 NYLON
CONTACT: BRASS

FINISH
仕上

SEE TABLE

DWN
T.SHINOHARA

31AUG07

CHK
K.BETSUI

31AUG07

APVD
K.BETSUI

31AUG07

PRODUCT SPEC
製品規格

APPLICATION SPEC
取付適用規格

WEIGHT
0

CUSTOMER DRAWING

TE Connectivity

9P HORIZONTAL TYPE CAP HOUSING ASS'Y
MULTI-INTERLOCK CONN. (WIRE TO P.C.B.)

SIZE
A2

CAGE CODE
00779

DRAWING NO
番号
171894

RESTRICTED TO
—

SCALE
尺度
2:1

SHEET
1 of 1

REV
E3

171894

B

A