

Article details		
Approvals		
Downloads/Certificates		
Accessories		
Description		
Remarks		
Item properties		
2-conductor through terminal block; 2.5 mm², suitable for Ex i applications; center marking; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®		
Miscellaneous		
Name	Value	Unit
Connection technology	CAGE CLAMP®	
Actuation type	Operating tool	
Connectable conductor materials	Copper	
Solid conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG	
Fine-stranded conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG	
Strip length	8 ... 9 mm (0.31 ... 0.35 inch)	
Total number of connection points	2	
Total number of potentialis	1	
Number of levels	1	
Type of wiring	Front-entry wiring	
Note (conductor cross-section)	12 AWG, THHN, THWN	
Width	5 mm / 0.197 in	
Height from upper-edge of DIN-35 rail	28 mm / 1.102 in	
Depth	53 mm / 2.087 in	
Design	horizontal	
Type of mounting	Carrier rail 35 x 15	
Marking level	Center marking	
Color	blue	
Insulating material	Polyamide 66 (PA 66)	
Fire load [MJ]	0.106	MJ
Weight [g]	5.676	g
Packaging type	BOX	
mm)	5	mm
Main product function	Through term. block	
Product type	Through rail-mount term. blocks	

Upwards