

Coaxial Cable Connector 16_QMA-50-2-3/133_N

Description

Right angle cable plug

Interface standards
QMA QLF compliant



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	11 GHz		
Frequency range	DC to 2.5 GHz	2.5 to 4 GHz	4 to 6 GHz
Return loss	30 dB	26 dB	20 dB

Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0069 kg

Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Bronze	SUCOPLATE (R) Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00007405
Catalogue drawing	DOU-00007407
Assembly instruction	DOC-0000178738

Ordering Information

Bulk 100 pcs package	16_QMA-50-2-3/133_NH
----------------------	----------------------

Additional Information

Suitable cables	SUCOFORM_86, EZ_86_TP_M17, MULTIFLEX_86
-----------------	---