

Coaxial Cable Connector 24_BNC-75-2-1/133_N

Description

Straight bulkhead cable feed through

Interface standards

Interface compatible with IEC 61169-8

Technical Data

Electrical Data

Impedance	75 Ω
Interface frequency max.	1 GHz

Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0204 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00009159
Catalogue drawing	DCA-00009161
Assembly instruction	DOC-0000179064
Mounting hole	DOU-00008751

Ordering Information

Single package	24_BNC-75-2-1/133_NE
----------------	----------------------

Additional Information

Suitable cables	RG_179_B/U, ENVIROFLEX_179, RG_187_A/U
-----------------	--