

Between Series Adaptor 34_MMBX-QMA-50-2/1--_N

Description

Adaptor jack/jack
MMBX jack (female) / QMA jack (female)

QuickLock Interface

Interface standards
Series MMBX - SUHNER-MMBX
Series QMA - QMA QLF compliant



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	12.4 GHz

Mechanical Data

Number of matings	100
Weight	0.0054 kg

Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - MMBX jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO / Gold Plating
Outer contact	Brass	SUCOPRO / Gold Plating
Body	Brass	SUCOPRO / Gold Plating
Insulator	LCP (Liquid crystal polymer)	

Interface - QMA jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO / Gold Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00126244
-----------------	--------------

Ordering Information

Tray package	34_MMBX-QMA-50-2/1--_NY
--------------	-------------------------