

Within Series Adaptor 32_MMBX-50-0-12/111_N

Description

Adaptor plug/plug
MMBX plug (male) / MMBX plug (male)

Slide - snap interface

Interface standard
Series MMBX - SUHNER-MMBX



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	12.4 GHz

Mechanical Data

Number of matings	100
Weight	0.0002 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - MMBX plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	Gold Plating (Nickel underplated)
Body	Bronze	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Interface - MMBX plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	Gold Plating (Nickel underplated)
Body	Bronze	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00018483
-----------------	--------------

Ordering Information

Bulk 100 pcs package	32_MMBX-50-0-12/111_NH
----------------------	------------------------