

Coaxial Cable Connector 21_SMB-50-2-11/111_N

Description

Straight cable jack

Interface standards

IEC 60169-10_MIL-STD-348A/311_CECC 22130



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0018 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

Related Documents

Catalogue drawing	DOU-00005883
Assembly instruction	DOC-0000179013

Ordering Information

Single package	21_SMB-50-2-11/111_NE
----------------	-----------------------

Additional Information

Suitable cables	K_02252_D, ENVIROFLEX_316_D, G_02232_D
-----------------	--