

Coaxial PCB Connector 82_QMA-50-0-3/111_N

Description

Straight PCB jack

Interface Standards
QMA QLF compliant



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Board mounting type	through holes
Weight	0.0013 kg

Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00012676
Catalogue drawing	DCA-00012678
Mounting hole	DOU-00002524

Ordering Information

Bulk 100 pcs package	82_QMA-50-0-3/111_NH
Tape and Reel package	82_QMA-50-0-3/111_NM

Remarks

PCB connector with stand-offs