

## Coaxial Cable Connector 11\_N-50-3-51/133\_N

### Description

Straight cable plug

Interface standards

IEC 61169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	18 GHz

#### Mechanical Data

Centre contact	plugged
Outer contact	soldered
Weight	0.0435 kg

#### Environmental Data

Operating temperature	-55 °C to 70 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	Air Dielectric - Bead - PPH	
Coupling nut	Brass	SUCOPLATE (R) Plating

### Related Documents

Catalogue drawing	DOU-00007863
Assembly instruction	DOC-0000180866

### Ordering Information

Single package	11_N-50-3-51/133_NE
----------------	---------------------

### Additional Information

Suitable cables	SUCOFORM_141, EZ_141_TP_M17, MULTIFLEX_141
-----------------	--